




# Most Popular Commodity Thermowells

**Special Low Prices**

If you do not see the thermowell you require in high volume, consult OMEGA Custom Engineering Department for a quotation.


**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

## Series 260L—Lagging Extension Type



\* NPSM internal pipe thread will accept both NPT and NPS male threads.


## Series 260S—General Use



\* NPSM internal pipe thread will accept both NPT and NPS male threads.

All models shown close to actual size.

## Series 260—Limited Space Type



# Most Popular Commodity Thermowells



B

If you do not see the thermowell you require in high volume, consult OMEGA Custom Engineering Department for a quotation.



**Consult OMEGA for all your high volume thermowell applications.**

We produce these wells in high volume for significant cost savings. They are made from the finest materials and meet our stringent quality standards.

**Connection Size:** 1/2 and 3/4 NPT are standard. Other thread sizes are available upon request.

**Materials:** Brass (ASTM B-16); stainless steel A.I.S.I. 304 and A.I.S.I. 316. Wells are also available in special materials; prices on request.

**Protective Coatings for Thermowells:** OMEGA can add a protective coating of PFA.

Contact OMEGA Custom Engineering for a quotation.



**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)						
Ext Thread	Model Number	Price	Material	Well Type	Insert Lgth.	Stem Lgth.
1/2 NPT	1/2-260L-U21/2-304SS-F	£16.75	304 SS	260L	2 1/2"	6"
	1/2-260L-U21/2-316SS-F	20	316 SS	260L	2 1/2"	6"
1/2 NPT	1/2-260S-U21/2-304SS-F	14.75	304 SS	260S	2 1/2"	4"
	1/2-260S-U21/2-316SS-F	18	316 SS	260S	2 1/2"	4"
	1/2-260S-U21/2-BRASS-F	13.50	Brass	260S	2 1/2"	4"
	1/2-260S-U41/2-304SS-F	16.75	304 SS	260S	4 1/2"	6"
	1/2-260S-U41/2-316SS-F	20	316 SS	260S	4 1/2"	6"
	1/2-260S-U71/2-304SS-F	20	304 SS	260S	7 1/2"	9"
3/4 NPT	3/4-260L-U21/2-304SS-F	18.75	304 SS	260L	2 1/2"	6"
	3/4-260L-U41/2-304SS-F	21.50	304 SS	260S	4 1/2"	9"
3/4 NPT	3/4-260S-U21/2-304SS-F	16.75	304 SS	260S	2 1/2"	4"
	3/4-260S-U21/2-316SS-F	20	316 SS	260S	2 1/2"	4"
	3/4-260S-U21/2-BRASS-F	13.50	Brass	260S	2 1/2"	4"
	3/4-260S-U41/2-304SS-F	18.75	304 SS	260S	4 1/2"	6"
	3/4-260S-U41/2-316SS-F	22	316 SS	260S	4 1/2"	6"
	3/4-260S-U71/2-304SS-F	23.50	304 SS	260S	7 1/2"	9"
3/4 NPT	3/4-260A-U15/8-304SS-F	13.50	304 SS	260A	1 5/8"	2 1/2"

10 piece minimum order. Prices subject to change due to fluctuations in material and other costs. Check for price at time of order.

**Ordering Example:** Quantity 10, 3/4-260S-U712-304SS-F, 304 stainless steel thermowell with 3/4 NPT external thread, 0.260" internal diameter, 7 1/2" insertion length and a 9" stem length, £23.50.

For Assistance in Choosing Head and Well Assemblies, See Guide on Page B-5. These wells are compatible with OMEGA® NB1, NB2, (page B-7); PR-12, PR14, and NPT-style probes, (page C-65); as well as DialTemp™ Thermometers (page E-14). PFA coating available, see page B-14.

**Increase Response Rate!**  
Use OT-201 Conductive Silicon Paste;  
see page B-36.

Pressure-Temperature rating—lb per square inch

Material	Temperature — °F						
	70°	200°	400°	600°	800°	1000°	1200°
Brass	2810	2530	440	—	—	—	—
A.I.S.I. 304	4120	3740	3400	3280	3180	2750	990
A.I.S.I. 316	4120	4120	3850	3760	3680	3080	1490

Discount Schedule	
1-10.....	Net
25-100.....	20%
11-24.....	10%
101 and up.....	Consult Sales

Discounts apply to similar thermowells.

See Page B-15 For Maximum Fluid Velocity.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany

0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters