

# Non-Reversible OMEGALABEL® Temperature Monitors

## Micro-Dot Series

(Model number is °F temperature rating preceded by letters "MD")

5 mm (0.2") Outside Diameter

1.3 mm (0.05") Indicating Window

## Bulls-Eye Series

(Model number is temperature rating preceded by letters "BE")

10 mm (0.4") Outside Diameter

3 mm (0.13") Indicating Window

## Specifications

**Accuracy:** Up to 99°C (210°F) is ±1°C (1.8°F); From 100°C (212°F) to 154°C (309°F) is ±1.5°C (2.7°F); From 160°C (320°F) to 280°C (536°) is ±1% and ±1°C (1.8°F)

Price  
pkg of 10    pkg of 30  
**£840**      **£2150**



MD labels shown  
actual size.

**Micro-Dot Series and Bulls-Eye Series are available in single temperature ratings listed below:**

°C	38	43	49	52	54	60	66	71	77	79	82	88	93
°F	100	110	120	125	130	140	150	160	170	175	180	190	200

°C	99	104	107	110	116	121	127	132	135	138	143	149
°F	210	220	225	230	240	250	260	270	275	280	290	300


To order package of 30, add "-30" to model number.

**Ordering Examples:** BE-210F-30, bulls-Eye label, 99°C (210°F), package of 30, £18.75. MD-100F-30, micro-dot label, 38°C (100°F), package of 30, £21.50.

Price  
pkg of 10    pkg of 30  
**£740**      **£1880**



BE labels shown  
actual size.



Shown smaller than actual size.

Four temperature ratings on each label

**4A:** 5.6°C (10°F) between each rating

**4B:** 11.1°C (20°F) between each rating

**4C:** 27.8°C (50°F) between each rating

Price  
pkg of 10  
**£940**  
pkg of 30  
**£27**

To order package of 30, add suffix "-30" to model number.

**Ordering Example:** 4A-100-30, low range temperature label, 38, 43, 49, 54°C (100, 110, 120, 130°F), package of 30, £27.

## Specifications

**Accuracy:** Up to 99°C (210°F) is ±1°C (1.8°F); From 100°C (212°F) to 154°C (309°F) is ±1.5°C (2.7°F); From 160°C (320°F) to 280°C (536°) is ±1% and ±1°C (1.8°F)

## 4A, 4B, 4C Labels (4 Temperatures per label)

Model No.	Temperature Ratings				
4A-100	°C	38	43	49	54
	°F	100	110	120	130
4A-110	°C	43	49	54	60
	°F	110	120	130	140
4A-120	°C	49	54	60	66
	°F	120	130	140	150
4A-130	°C	54	60	66	71
	°F	130	140	150	160
4A-140	°C	60	66	71	77
	°F	140	150	160	170
4A-150	°C	66	71	77	82
	°F	150	160	170	180
4A-170	°C	77	82	88	93
	°F	170	180	190	200
4A-180	°C	82	88	93	99
	°F	180	190	200	210
4A-190	°C	88	93	99	104
	°F	190	200	210	220
4A-210	°C	99	104	110	116
	°F	210	220	230	240
4A-220	°C	104	110	116	121
	°F	220	230	240	250
4A-230	°C	110	116	121	127
	°F	230	240	250	260
4A-270	°C	132	138	143	149
	°F	270	280	290	300
4A-280	°C	138	143	149	154
	°F	280	290	300	310
4A-310	°C	154	160	166	171
	°F	310	320	330	340
4A-320	°C	160	166	171	177
	°F	320	330	340	350
4B-100	°C	38	52	66	79
	°F	100	125	150	175
4B-125	°C	52	66	79	93
	°F	125	150	175	200
4B-150	°C	66	79	93	107
	°F	150	175	200	225
4B-175	°C	79	93	107	121
	°F	175	200	225	250
4B-200	°C	93	107	121	135
	°F	200	225	250	275

## MOST POPULAR MODELS HIGHLIGHTED!

Model No.	Temperature Ratings				
4B-225	°C	107	121	135	149
	°F	225	250	275	300
4C-100	°C	38	66	93	121
	°F	100	150	200	250
4A-350	°C	177	182	188	193
	°F	350	360	370	380
4A-370	°C	188	193	199	204
	°F	370	380	390	400
4B-250	°C	121	135	149	163
	°F	250	275	300	325
4B-300	°C	149	163	177	191
	°F	300	325	350	375
4B-350	°C	177	191	204	218
	°F	350	375	400	425
4B-375	°C	191	204	218	232
	°F	375	400	425	450
4B-425	°C	218	232	246	260
	°F	425	450	475	500
4C-200	°C	93	121	149	177
	°F	200	250	300	350
4C-250	°C	121	149	177	204
	°F	250	300	350	400
4C-300	°C	149	177	204	232
	°F	300	350	400	450
4C-350	°C	177	204	232	260
	°F	350	400	450	500

## Discount Schedule (Packs)

1 to 9	.....	Net
10 to 49	.....	.10%
50 to 99	.....	.20%
100 to 499	.....	.30%
500+	.....	Consult Sales



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters