

Handheld Digital Thermometers Type R and S Thermocouple Inputs



HH501BR/HH501BS

£57



**HH501BR or HH501BS
Type Thermometer**
1999 Counts
Backlit LCD Display
Models for Type R or S
Thermocouple Input
Reading HOLD, Max
function
Dual input with Differential
Function T1-T2

HH501BS, £57, shown
smaller than actual
size.

Probes sold
separately.
Please see
Section A for
details.

- ✓ IP65 Dustproof
- ✓ Water/Splash Resistant
- ✓ Warning Beeper
with Hi/Lo Setting,
Time Setting
- ✓ Clock and Elapsed Time
- ✓ 0.1° Resolution
- ✓ Differential
Thermocouple Input
- ✓ Stated Accuracy at
23 ± 5°C < 75% RH
- ✓ Battery Life: 200 Hours
- ✓ Dimensions:
192 H x 91 W x 53 mm D
- ✓ Weight:
Approx. 255 g



HH501AR

£50



**HH501AR
Thermometer**
1999 counts,
Backlit LCD Display
Type R Thermocouple
Input
Reading HOLD and
MAX function
ITS-90 Accuracy: ± 0.2%
Single Input

HH501AR, £50, shown
smaller than actual
size.

Specifications	HH501BS	HH501AR	HH501BR
Backlit LCD	•	•	•
No. of Digits	1999	1999	1999
Probe (Type)	S	R	R
Input Channel	2	1	2
Range °C	0-1767°C	0-1767°C	0-1787°C
Range °F	32-1999°F	32-1999°F	32-1999°F
Resolution	1°	1°	1°
Data/Hold	•	•	•
Max/Min	•	•	•
Relative	•	•	•
Hi/Lo Limits w/Beeper Warning	•	•	•
Display	1	1	1
T1-T2	•	•	•
Battery	9 V	9 V	9 V
Auto Power Off	•	•	•
Basic Accuracy % rdg	0.1% +1°C	0.1% +1°C	0.1% +1°C

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
HH501BS	£57.00	Thermometer, S T/C, dual input
HH501AR	50.00	Thermometer, R T/C, single input
HH501BR	57.00	Thermometer, R T/C, dual input
CAL-3-HH	50.00	Traceable calibration certificate
MN1604	2.00	Extra 9 V alkaline battery
SC-HH500	8.00	Soft carrying case