


RTD Probes with Transitions

Starts at
£24



- ✓ Probe Transition Includes a Strain Relief Spring at the Cable Exit
- ✓ Available in Imperial and Metric Diameters
- ✓ Temperature Range -200 to 600°C (Transition and Cable to 260°C Max)
- ✓ High-Accuracy 100 , Class “A” DIN Platinum Elements per IEC 751 (alpha = 0.00385 / °C)
- ✓ 2-, 3-, and 4-Wire Constructions Available



MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)					
Model Number	Lead Wire Style	Sheath Length	Price		
			6 mm Dia.	4.5 mm Dia.	3 mm Dia.
PR-11-2-(*)-150	3 Wire	150 mm	£24	£25	£25
PR-11-2-(*)-225	3 Wire	225 mm	25	26	26
PR-11-2-(*)-300	3 Wire	300 mm	25	26	26
PR-11-2-(*)-450	3 Wire	450 mm	27	28	28
PR-11-2-(*)-600	3 Wire	600 mm	28	29	29

* Specify “-M30” for 3 mm, “-M45” for 4.5 mm or “-M60” for 6 mm for probe diameter in millimetres. To order probes in intermediate lengths, change model number, using next longer probe price. Over 600 mm, add £2.50 per 100 mm of probe length. For longer leads, add the lead length in metres to the model number and £2 per metre.

Ordering Example: PR-11-2-M45-150-MTP, 100 , class “A” RTD with a 4.5 mm diameter by 150 mm long probe, 1 m of 3-wire cable and MTP connector, £25 + 4.70 = £29.70.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters