

# High-Accuracy Fluid Immersion RTD Sensors


## For Use in Monitoring Temperature in Fluid and Pressurized Applications

Starts at  
**\$79**



- ✓ Provided with High-Accuracy Class "A" 100 Element (Standard)
- ✓ Stainless Steel Probe Stem and Mounting Fitting (1/8" NPT) Provided

- ✓ Usable Temperature Range: -200 to 750°C (Cable to 232°C)
- ✓ 3-Wire Construction for Connecting to Most Instruments




**MOST POPULAR MODEL HIGHLIGHTED!**

To Order (Specify Model Number)					
Model Number	Sensing Element		Cable	Max Temperature	Price
RTD-810	100	Class "A" DIN	1 m (40") Long PFA Insulated	750°C (Cable 232°C)	<b>\$79</b>
RTD-810-OTP	100	Class "A" DIN	1 m (40") Long PFA with OTP Connector	750°C (Cable 232°C)	<b>86</b>
RTD-810-TA3F	100	Class "A" DIN	1 m (40") Long PFA with TA3F Connector	750°C (Cable 232°C)	<b>96</b>

**Terminations Available:** Provided with standard miniature connector; for larger sized connector, add "-OTP" to model number and \$7 to price; for audio connector, add "-TA3F" to model number and \$17 to price.

**Ordering Example:** RTD-810-OTP, Class "A" accuracy with heavy-duty connector, \$79 + 7 = \$86. RTD-810-TA3F, Class "A" accuracy with audio connector, \$79 + 17 = \$96.

### Popular Options Include:



OTP-U-M, Heavy-Duty Connector, \$7. See page G-11.



TA3F, Connector, \$17. See page G-54.



HH505, Handheld Thermometer, \$75. See page L-62.



TX904, Transmitter, \$173. See page N-15.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters