

# 1/16 DIN Autotune Controller

Panel punches available, visit [omega.com/panelpunches](http://omega.com/panelpunches)



KMTSS-125G-6 thermocouple sold separately, \$24, see page A-81.

Single Output Model  
**\$440**

Dual Output Model  
**\$465**

CN76030, \$440, shown larger than actual size.

*High Performance in a Small Package!*

CN76000 Series Starts at  
**\$440**



- ✓ Dual 4-Digit Display
- ✓ Autotune PID, PID, or On/Off Control
- ✓ Thermocouple Input with 1° or 0.1° Resolution
- ✓ RTD Input with 1° or 0.1° Resolution
- ✓ Scalable Voltage and Current Inputs
- ✓ Displays in °F, °C, or Engineering Units
- ✓ Password Protection


- ✓ Front-Panel Programming
  - ✓ Relay, DC Pulse, AC SSR, Voltage, or Current Output(s)
- Optional Features
- ✓ Analog Process or RS485 Digital Output
  - ✓ Tracking/Non-Tracking Alarms
- Additional Features
- ✓ Loop Break Protection
  - ✓ Min/Max Indication
  - ✓ Auto/Manual Operation
  - ✓ Percent Output Indication
  - ✓ Single-Segment Ramp and Soak




Compact, 1/16 DIN Size, with NEMA 2, 3R, and 12 Rated Front Panel.



CN76030, compact 1/6 DIN size, \$440, shown actual size.



Convenient screw terminal connections.



The CN76000 1/6 DIN controllers provide economical control for a wide variety of processes, including heating, cooling, and heat/cool. When used with the proper transmitters, these devices can also control pressure, flow, humidity, motion, or pH. The front panel is NEMA 2, 3R, and 12 rated for waterproof protection and is corrosion resistant.

The sophisticated design of the CN76000 incorporates the latest microprocessor and surface mount technology, compressing an unprecedented number of standard features into a compact 1/6 DIN package. The user can program control functions from the front panel; input types are DIP switch selectable. Multiple tuning modes allow the user to select from 3 standard tuning presets, manual tuning, or autotuning.

Standard features include self-diagnosis with fault indication. Non-volatile memory retains all process parameters when power is off, without battery backup. Settings for the optional alarm are configurable. The alarm action may be defeated on startup, or until the process value exceeds the alarm setpoint. The power interrupt feature will reset on power-up if the alarm condition no longer exists.

Other standard features include min/max storage and display, auto/manual control, percent output indication, ramp and soak operation, 4 user-selectable security levels with password protection, and jumper-selected 5 Vdc pulse output to drive external solid state relays. Optional features include RS485 communications, process recorder output, and 4-stage setpoint.

## Specifications

**Inputs:** Thermocouple, RTD, voltage or current; see input chart for ranges

**Resolution:** See range chart; voltage and current input models are fully field scalable to engineering units with up to 2 decimal places

**Accuracy:**  $\pm 0.25\%$  span  $\pm 1$  digit

**Input Impedance:** 3 M $\Omega$  min, thermocouple; 200  $\mu$ A, RTD current; 249  $\Omega$ , current; 5 k $\Omega$ , voltage

### Sensor Break Protection:

De-energizes control outputs to protect system

### Loop Break Protection:

Error message is initiated on shorted sensor or open heater circuit; break time adjustable from off to 99 min.

**Loop Break Alarm:** On alarm relay equipped units, unit can be programmed to alarm on loop break

**Setpoint Range:** Selectable

**Displays:** Dual 4-digit, 7-segment LED, 7.6 mm (0.3") high; process variable in red, setpoint in green

**Control Action:** Reverse (heat) or direct (cool) action; selectable for single or dual setpoint models

**Control Modes:** Time-proportioning and proportional control modes; selectable preset tune, autotune or manual PID, P, PI or PD with reset anti-windup

**Proportional Band:** 6 to 5000 $^{\circ}$ F or equivalent  $^{\circ}$ C units; 6 to 9990 for voltage/current inputs

### Integral Time:

0.1 to 99.9 minutes, or off

### Derivative Time:

0.01 to 99.99 minutes, or off

### Cycle Time:

2 to 80 s

### Approach Rate:

Off to 99.99 min

**On-Off Control:** Adjustable on-off differential 2 $^{\circ}$  to full scale in 1 $^{\circ}$  steps, 2 counts to full scale in 1-count steps (voltage/current inputs)

**Ramp and Soak:** One ramp time and soak time each adjustable from 0 to 100 hours; end procedure can be set for HOLD or OFF

### Power:

85 to 265 Vdc or Vac, 50 to 400 Hz

**Power Consumption:** 5 VA max

### Line Voltage Stability:

$\pm 0.05\%$  over supply voltage range

### Temperature Stability:

4  $\mu$ V/ $^{\circ}$ C (2.3  $\mu$ V/ $^{\circ}$ F) typical,



8  $\mu$ V/ $^{\circ}$ C (4.5  $\mu$ V/ $^{\circ}$ F) max

### Common-Mode Rejection:

140 dB minimum at 60 Hz

### Normal-Mode Rejection:

65 dB typical, 60 dB at 60 Hz



**Isolation:** Relay and SSR outputs are isolated; current, voltage and logic outputs must not share common grounds with the input

### Memory:

Non-volatile; no batteries required

**Mechanical Relay Output:** SPST (form A), 3 A @ 250 Vac, resistive; 1.5 A @ 250 Vac, inductive; 250 VA pilot duty rating, 2 A @ 125 Vac or 1 A @ 250 Vac, 1/8 hp @ 125 Vac or 250 Vac

**Solid State Relay Output:** 3.5 A up to 240 Vac at 25 $^{\circ}$ C (77 $^{\circ}$ F); derates to 1.25 A @ 55 $^{\circ}$ C (131 $^{\circ}$ F)

### Voltage Output:

Non-isolated; 0 to 10 Vdc, 500  $\Omega$  min

**Current Output:** Non-isolated; 0 to 20 mA, 600  $\Omega$  max; zero and span adjustable

### DC Pulse Output:

Non-isolated; 5 Vdc @ 25 mA

**Operating Ambient:** -10 to 55 $^{\circ}$ C (-4 to 131 $^{\circ}$ F); 0 to 90% RH up to 40 $^{\circ}$ C (104 $^{\circ}$ F), non-condensing; 10 to 50% at 55 $^{\circ}$ C (131 $^{\circ}$ F), non-condensing

### Storage Ambient:

-40 to 80 $^{\circ}$ C (-40 to 175 $^{\circ}$ F)

**Alarms:** 2 alarms operate the same relay; 3.0 A resistive 250 Vac; form A contact (SPST); field programmable for absolute (non-tracking) or deviation (tracking); can be set anywhere within the scaling of the controller; selectable inhibit and power interrupt; automatic/manual reset

**Process Signal Output (Optional):** Linearized, non-isolated

0 to 10 Vdc @ 5 mA; user-selectable scale positioning of zero and full scale; scaling span is 50 to 11,998 counts

### RS485 Communications

**(Optional):** Unit with RS485 compatible communications (no CE rating for RS485 option)

**Dimensions:** 48 H x 48 W x 125 mm D (1.88 x 1.88 x 4.925"); 115.3 mm (4.54") depth behind panel

### Panel Cutout:

45 mm (1.775") square; 1/6 DIN

**Weight:** 227 g (8 oz)

**Front-Panel Ratings:** NEMA 2, 3R and 12; dust and splash resistant

## Input Types and Ranges

Input Type		Range	Resolution	Range	Resolution
<b>J DIN</b>	Iron-constantan	-100 to 1600°F -100 to 990°F	1°F 0.1°F	-73 to 87°C -73 to 871°C	1°C 0.1°C
<b>J</b>	Iron-constantan DIN	-100 to 1600°F -100 to 990°F	1°F 0.1°F	-73 to 87°C -73 to 871°C	1°C 0.1°C
<b>K</b>	CHROMEGA®-ALOMEGA®	-200 to 2500°F -190 to 990°F	1°F 0.1°F	-129 to 137°C -129 to 990°C	1°C 0.1°C
<b>E</b>	CHROMEGA®-constantan	-100 to 1800°F -100 to 990°F	1°F 0.1°F	-73 to 982°C -73 to 990°C	1°C 0.1°C
<b>T</b>	Copper-constantan	-350 to 750°F -190 to 750°F	1°F 0.1°F	-212 to 398°C -212 to 398°C	1°C 0.1°C
<b>R</b>	OMEGALLOY® nicrosil-nisil	-100 to 2372°F -100 to 990°F	1°F 0.1°F	-73 to 1300°C -73 to 990°C	1°C 0.1°C
<b>N*</b>	Pt/13%Rh-Pt	0 to 3200°F	1°F	-17 to 1760°C	1°C
<b>C*</b>	Pt/10%Rh-Pt	0 to 3200°F	1°F	-17 to 1760°C	1°C
<b>S</b>	Pt/6%Rh-Pt/30%Rh	75 to 3308°F	1°F	24 to 1820°C	1°C
<b>B</b>	W/5%Re-W/26%Re	0 to 4208°F	1°F	-17 to 2320°C	1°C
<b>RTD</b>	100 Ω Pt 0 0385 curve	-328 to 1607°F -190 to 990°F	1°F 0.1°F	-200 to 875°C -190 to 875°C	1°C 0.1°C
<b>RTD</b>	100 Ω Pt 0 0392 curve	-328 to 1607°F -190 to 990°F	1°F 0.1°F	-200 to 875°C -190 to 875°C	1°C 0.1°C
<b>RTD</b>	120 Ω Ni	-112 to 608°F -112 to 608°F	1°F 0.1°F	-80 to 320°C -80 to 320°C	1°C 0.1°C
<b>Process Current</b>		0 to 20 mA, 4 to 20 mA <sup>†</sup>			
<b>Process Voltage</b>		0 to 5 Vdc, 1 to 5 Vdc <sup>†</sup>			

<sup>†</sup> Voltage and current inputs are fully scalable for zero and span.  
Maximum setting range is -1999 to 9999 counts.

**MOST POPULAR MODELS HIGHLIGHTED!**

## Options

Ordering Suffix	Add'l Price	Description
-PV	\$81	Scalable recorder; output 0 to 10 Vdc
-485A**	100	RS485 communications

**Note:** Only 1 option may be installed in a unit.  
\*\* No CE rating for -485A option.



Recommended Reference Book:  
Controller Tuning PID Without Math,  
GE-2117, \$23. See Section Y for  
Additional Books.



## To Order (Specify Model Number)

### Single Output Models

Model No.	Price	Output
<b>CN76(*)30</b>	<b>\$440</b>	Relay/DC Pulse <sup>††</sup>
<b>CN76(*)20</b>	<b>440</b>	DC pulse/AC SSR <sup>††</sup>
<b>CN76(*)50</b>	<b>455</b>	0 to 20 mA
<b>CN76(*)60</b>	<b>455</b>	0 to 10 Vdc

Comes complete with mounting bracket and operator's manual.

\* Specify 0 for standard unit, 1 for alarm unit; for alarms, add \$25 to price.

<sup>††</sup> These outputs are logic jumper selectable between relay and DC pulse, or between DC pulse and AC SSR.

**Ordering Example:** CN76030-485A, CN76000 controller with single relay/DC pulse output and optional RS485 communications, \$440 + 100 = \$540.

### Dual Output Models

Model No.	Price	Output 1	Output 2
<b>CN76(*)33</b>	<b>\$465</b>	Relay/DC pulse <sup>††</sup>	Relay/DC pulse <sup>††</sup>
<b>CN76(*)22</b>	<b>465</b>	DC pulse/AC SSR <sup>††</sup>	DC pulse/AC SSR <sup>††</sup>
<b>CN76(*)53</b>	<b>485</b>	0 to 20 mA	Relay/pulse <sup>††</sup>
<b>CN76(*)63</b>	<b>485</b>	0 to 10 Vdc	Relay/DC pulse <sup>††</sup>

\* Specify 0 for standard unit, 1 for alarm unit; for alarms, add \$35 to price.

<sup>††</sup> These outputs are logic jumper selectable between relay and DC pulse, or between DC pulse and AC SSR.

**Ordering Example:** CN76133-485, CN76000 controller with dual relay/DC pulse outputs, alarms and optional RS485 communications, \$465 + 35 + 100 = \$600.

## Accessories

Model No.	Price	Description
<b>DPP-4</b>	<b>\$475</b>	1/16 DIN panel punch
<b>CNQUENCHARC</b>	<b>8</b>	Noise suppression kit for mechanical relay models driving AC contactors or solenoids

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters