



Contact/Non-Contact Pocket Laser Tachometer with Totaliser/Counter/Timer Features

HHT13
£144



- ✓ Operating Range Up to 7.6 m (25') (Class 3R Visible Laser)
- ✓ Supports Remote Contact Assembly, Standard in the Kit
- ✓ Accepts Optional Remote Sensors
- ✓ TTL Pulse Output
- ✓ Auto-Ranging/Fixed Decimal (User Selectable)
- ✓ English and Metric Rates
- ✓ Tripod Mounting Bushing
- ✓ On-Target and Low-Battery Indicators
- ✓ Rugged Rubberized Housing
- ✓ Traceable Certificate of Calibration Included

Specifications

Display: 5-digit alphanumeric LCD
Range:

Optical: 5 to 200,000 rpm
Contact*: 0.5 to 20,000 rpm
(Other ranges: inches, feet, yards, miles, cm, m, per hour, minutes, seconds)

Accuracy:

Optical: ±0.01% of reading
Contact*: ±0.05% of reading (rpm)

Resolution: 0.001 to 10 rpm (speed range dependent)

Operating Range: 50 mm to 7.6 m (2" to 25')

Memory: Max, min and last

Power: 2 "AA" 1.5 Vdc batteries (included)

Environmental: 5 to 40°C (41 to 104°F), 80% RH up to 30°C (86°F)

Dimensions: 176 x 61 x 41 mm (6.9 x 2.4 x 1.6")

Weight: 210 g (7 oz)



HHT13, £144, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

The HHT13 is a digital, battery-powered, optical pocket laser tachometer that operates up to 7.6 m (25') from a reflective target using a laser light source. The ergonomic design allows safe, direct line-of-sight viewing of both the target and the display, while providing a no-slip rubber surface for single-hand operation. The HHT13 is a 32-function tachometer/ratemeter, totaliser/counter, and timer (stopwatch), which is programmable in both imperial and metric rates. Support is built-in for the optional remote contact assembly (RCA) and the plug-in remote sensors. The HHT13 has a TTL-compatible pulse output to trigger devices such as data collectors and stroboscopes.

OMEGACARESM extended warranty programme is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labour and equivalent loaners.

To Order (Specify Model Number)		
Model No.	Price	Description
HHT13	£144	Tachometer/timer/totaliser with calibration certificate
HHT13-KIT	200	Tachometer/timer/totaliser with calibration certificate, RCA, carrying case
HHT20-ROS	95	Remote optical sensor with 2.4 m cable, mounting bracket and 300 mm of reflective tape
HHT13-CC10	16.75	Padded pouch fits tachometers
HHT13-RCA	37	RCA includes contact tips (concave and convex) and 10 cm linear contact wheel
HHT13-CTE	6.70	Rubber concave, convex tips and 10 cm contact wheel
HHT13-LCW	30	Linear contact wheel with 305 mm (12") circumference for use with RCA
HHT-RT-5	8.70	Reflective tape 1.5 m roll, 12 mm wide
MA-1214	84	Reference Book: Statistical Intervals

* With optional RCA.

Comes with traceable certificate of calibration, two 150 x 12 mm strips of reflective tape, 2 "AA" batteries and operator's manual. The HHT13-KIT comes with operator's manual, traceable certificate of calibration, 2 "AA" batteries, 1.5 m roll of T-5 reflective tape, an RCA, including concave and convex tips, and a 10 cm linear contact wheel, all in a latching hardcover carrying case.

Ordering Examples: HHT13, tachometer, HHT-RT-5, spare reflective tape, MA-1214, reference book: Statistical Intervals, £144 + 8.70 + 84 = £236.70. Ocw-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (£36), £144 + 36 = £180.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters