

Platinum RTD Capsules



RTDCAP Series

- ✓ 4 Temperature Ranges Available
- ✓ 100 or 1 K Ω Available
- ✓ 2-, 3- and 4-Wire Configurations as Noted
- ✓ Moisture Resistant Available in Some Models

Ready to use platinum RTD capsules have insulated lead wires welded and anchored internally. No splicing to fragile elements is required. This construction assures reliable rugged embedment, insertion or probe assembly. Tip diameters from 0.086 to 0.125". Standard sensors and encapsulation materials rated up to 540°C (1000°F). Choose the moisture resistant version for condensing conditions.

Specifications

Operating Temperature Range:

TFE Leads: -200 to 260°C
(-320 to 500°F)

Polyimide Leads: -200 to 350°C
(-320 to 660°F)

Fiberglass Leads: -75 to 510°C
(-100 to 950°F)

Moisture Resistant: -50 to 200°C
(-60 to 390°F)

Sensing Element: International grade thin film platinum, $\alpha = 0.00385 \Omega/\Omega/^\circ\text{C}$ per IEC 60751

Ice Point Resistance: 100.00 \pm 0.06 Ω or 1000.0 \pm 0.6 Ω at 0°C

Time Constant (Water at 3"/Second):

0.086 Diameter = 0.5 seconds

0.098 Diameter = 0.6 seconds

0.125 Diameter = 0.8 seconds


0.187 Diameter = 1.5 seconds

Self-Heating: Greater than 15 mW/ $^\circ\text{C}$

Interchangeability/Accuracy:

Class A ($\pm 0.15 + .002 \cdot |t|$) [t = absolute value of temperature in $^\circ\text{C}$] between -50 and 300°C, Class B above and below these temperatures

Long Term Stability: Better than 0.05°C (0.02% of resistance) per 5 years, -50 to 300°C (-58 to 572°F), 0.25°C per year to 540°C (1004°F)



Insulation Resistance: Greater than 50 Megohms at 50 Vdc at 25°C (77°F)

Maximum Current: 100 Ω = 5 mA, 1000 Ω = 2 mA for limited self-heating; also suitable as self-heated sensors

Recommended Current: 1 mA maximum for temperature sensing


Case Materials: Alumina on 0.125 and 0.086 diameter, Polyimide [350°C (662°F)] on 0.098 diameter

Lead Materials, Nickel-Coated Copper-Insulated:

22/28 AWG Fiberglass: Rated to 510°C (950°F)

22/28 AWG TFE: Rated to 260°C (500°F)

28 AWG Polyimide: Rated to 350°C (660°F)



To Order Visit omega.com/rtdcap for Pricing and Details	
Model No.	Description
RTDCAP-100A-1-A086-060-K-40	100 Ω RTD, 0.086" diameter x 0.6" long alumina with 28 AWG polyimide leads, 350°C (660°F), 2-wire only
RTDCAP-100A-2-P098-050-K-40	100 Ω RTD, 0.098" diameter x 0.5" long polyimide with 28 AWG polyimide leads, 350°C (660°F), 3-wire only**
RTDCAP-100A-2-P098-050-T-40	100 Ω RTD, 0.098" diameter x 0.5" long polyimide with 28 AWG TFE leads, 260°C (500°F), 3-wire only**
RTDCAP-100A-3-A125-060-T-40	100 Ω RTD, 0.125" diameter x 0.6" long alumina with 28 AWG TFE leads, 260°C (500°F), 4-wire only**
RTDCAP-100A-2-A125-060-T-40-M	100 Ω RTD, 0.125" diameter x 0.6" long alumina with 28 AWG PFTE leads, 200°C (390°F), 300 psi seal, moisture resistant, 3-wire only**
RTDCAP-100A-2-A125-060-F-40	100 Ω RTD, 0.125" diameter x 0.6" long alumina with 28 AWG fiberglass leads, 510°C (950°F), 3-wire only**
RTDCAP-1KA-1-A086-060-K-40	1000 Ω RTD, 0.086" diameter x 0.6" long alumina with 28 AWG polyimide leads, 350°C (660°F), 2-wire only
RTDCAP-1KA-2-P098-050-K-40	1000 Ω RTD, 0.098" diameter x 0.5" long polyimide with 28 AWG polyimide leads, 350°C (660°F), 3-wire only**
RTDCAP-1KA-2-P098-050-T-40	1000 Ω RTD, 0.098" diameter x 0.5" long polyimide with 28 AWG TFE leads, 260°C (500°F), 3-wire only**
RTDCAP-1KA-3-A125-060-T-40	1000 Ω RTD, 0.125" diameter x 0.6" long alumina with 28 AWG TFE leads, 260°C (500°F), 4-wire only**
RTDCAP-1KA-2-A125-060-F-40	1000 Ω RTD, 0.125" diameter x 0.6" long alumina with 28 AWG fiberglass leads, 510°C (950°F), 3-wire only**

**** Note:** 3- and 4-wire sensors can be modified by the customer for 2- and 3-wire applications by cutting off unneeded lead wires.

Ordering Example: **RTDCAP-100A-2-P098-050-K-40**, 100 Ω RTD, 0.098" diameter x 0.5" long polyimide with 28 AWG Kaptor® (polyimide) leads, 350°C (660°F), 3-wire maximum.

RTDCAP-1KA-2-P098-050-K-40, 1000 Ω RTD, 0.098" diameter x 0.5" long polyimide with 28 AWG polyimide leads, 350°C (660°F), 3-wire.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters