



Strip Chart Recorders



All models shown smaller than actual size.

RD-87 Series Starts at **\$399**



- ✓ J Thermocouple, Temperature, Temperature/Humidity, Voltage, Current, 4 to 20 mA Input Models
- ✓ LCD Alphanumeric Display, 16 Characters 2-Line
- ✓ 100 mm (4") Strip Chart
- ✓ Metric (mm) or Standard (inch) Charts
- ✓ Probes are Field Interchangeable and Can be Extended
- ✓ Over/Under Alarm with Relay and Beeper, Selectable Delay Feature
- ✓ Battery Backup for Up to 48 Hours
- ✓ +12 Vdc for Mobile Applications Compatible

The OMEGA RD-87 Series strip chart recorders are offered in different models to record either a J Thermocouple, Temperature, Temperature/Humidity, Voltage, Current, or a 4 to 20 mA input signal on a 100 mm (4") wide strip chart, with a single pen. The temperature/humidity model uses two pens. Pens are colored to maximize chart readability. All RD-87 models offer a LCD display and user friendly controls. A full function alarm feature is provided on the RD-87 Series. The alarm can be set to sound an audible signal when the measured value(s) has exceeded an upper or lower limit. Each limit is individually set from the front panel. A delay time before the alarm is activated may be set by the user to prevent nuisance alarms caused by short-term variations. Low power normally open relay contacts are provided to allow activation of a remote alarm, phone dialer or annunciation.

Power is supplied through a 120 Vac 50/60 Hz plug-in adapter. External power may be supplied from any 12 Vdc source such as automotive, marine, or other battery. Battery backup for up to 48 hours is featured to provide operation during temporary power loss.



Specifications (General)

Operating Ambient Temperature

Range: 0 to 50°C (32 to 120°F)

Storage Temperature:

-18 to 50°C (0 to 120°F)

Primary Power: 115 Vac, 50/60 Hz adapter (220 to 240 Vac, 50 Hz optional)

Backup Power: 8 "AA" alkaline batteries (ordered separately)

Alternative Power: 12 V vehicle operation

Chart Strip Chart: 6 m x 120 mm (20' x 4 3/4"), roll type

Effective Recording Span: 100 mm (4")

Metric Paper Grid Lines: Time line every 5 mm with markings every 20 mm; 50 minor and 10 major divisions labeled on a rotating basis, with 100 to 0, 10 to 0, 20 to -30, 50 to 0, 60 to -40



Standard Paper Grid Lines: Time line every 0.25" with markings every 1"; 50 minor and 10 major divisions labeled on a rotating basis with 100 to 0, 60 to -40, 150 to 50, 250 to 0, 500 to 0

Remote Alarm Type: Normally open, 48 Vac/Vdc, 0.1 A dry contacts

Remote Alarm Connection: 2, ¼" terminal (spade) lugs in battery compartment area

Chart Speeds:

- ½ cm/hour, ¼"/hour
- 2 cm/hour, 1"/hour
- 4 cm/hour, 2"/hour
- 8 cm/hour, 4"/hour

- 16 cm/hour, 8"/hour
- ½ cm/min, ¼"/min
- 1 cm/min, ½"/min
- 2 cm/min, 1"/min
- 4 cm/min, 2"/min

Chart Speed Accuracy: ±1%

Alarm Delay Range: 0, 10, 20, 60, 120 min

Display: Alphanumeric LCD, 16 characters 2 line

RS232 Port Connection: RJ11 (4 pin) connector in battery compartment area

RS232 Port Parameters:

Data transmitted as measured, 4800 baud, 8, N, 1

Mounting: Vertical or horizontal, free standing or wall mounted

Dimensions: 235 x 184 x 50 mm (9.25 x 7.25 x 2")

Weight: 1.1 kg (2.5 lb)

Power Consumption: 3.5 W max

The RD-87-J is a precision strip chart recorder for recording temperature via a J Type thermocouple connected with a miniature (SMP) type connector located in the battery compartment area. A 6' beaded thermocouple fiberglass wire probe is supplied with the unit. Other probes, sold separately, are available as needed for high temperature or other application requirements.

Specifications (RD-87-J)

Temperature Accuracy: ±1°C (±2°F)

Temperature Ranges

°C	°F
-40 to 60	-40 to 60
-30 to 20	0 to 250
0 to 50	0 to 150
0 to 100	0 to 100
0 to 500	0 to 500
	0 to 1000



RD-87-J, \$399, shown smaller than actual size.

The RD-87-TRH is a precision temperature, relative humidity and dew point recorder with a digital display. The RD-87-TRH is menu driven and all parameters are shown on a 2-line alphanumeric LCD display. A temperature/humidity probe with 6' cable (2' coiled) is supplied with the unit to connect to an RJ14 (6 pin) connector located in the battery compartment area.

Specifications (RD-87-TRH)

Temperature Accuracy: ±1°C (±2°F)

Relative Humidity Accuracy: ±2% (0 to 95% RH)

Temperature Range: -40 to 60°C (-40 to 140°F)

Relative Humidity Range: 0 to 100%

Dewpoint: Calculated value

Probe Dimensions: 118 x 14 mm Dia. (4.6 x 0.55")

Chart Ranges

°C	°F
-40 to 60	-40 to 60
-30 to 20	50 to 150
0 to 50	0 to 100



RD-87-TRH, \$439, shown smaller than actual size.



The RD-87-TEMP is a precision strip chart recorder for recording temperature. The RD-87-TEMP features a proprietary temperature sensor that is enclosed with a 4" stainless steel jacket, which may be immersed in any solid or liquid that is compatible with 300 series stainless steel. The probe has 15' of cable and utilizes a standard RCA (stereo plug) jack to connect to the connector located in the battery compartment area.


Specifications (RD-87-TEMP)

Temperature Accuracy: $\pm 1^{\circ}\text{C}$ ($\pm 2^{\circ}\text{F}$)

Probe Dimensions: 72 x 5 mm Dia. (2.8 x 0.2") with pointed tip

Chart Ranges

$^{\circ}\text{C}$	$^{\circ}\text{F}$
-40 to 60	-40 to 60
-30 to 20	50 to 150
0 to 50	0 to 100



RD-87-TEMP, \$399, shown smaller than actual size.

The RD-87-VAC is a precision strip chart recorder for measuring and recording AC voltage using a true RMS converter. AC Voltage connections are available as two banana jacks on the side of the recorder case. Two 750 mm (30") wires, each with banana plug and alligator clip, are provided.

Specifications (RD-87-VAC)

AC Voltage Accuracy: ± 0.5 Vac

AC Voltage Alarm Range: 0 to 500 Vac

Chart Ranges

0 to 100 Vac
50 to 150 Vac
0 to 200 Vac
0 to 500 Vac



RD-87-VAC, \$399, shown smaller than actual size.

The RD-87-MA is a precision strip chart recorder for measuring and recording DC voltage and current. The RD-87-MA is specifically designed to record the output of 4 to 20 mA loop transmitters and voltage output transducers. The RD-87-MA is supplied with a removable screw type connector plug to facilitate connection to 4 to 20 ma current loops. The connector is located in the battery compartment area.

Range (Accuracy)

0 to 5.00 V	(± 0.01 V)
0 to 100 mV	(± 1 mV)
0 to 20 mA	(± 0.1 mA)
4 to 20 mA	(± 0.1 mA)



RD-87-MA, \$439, shown smaller than actual size.

The RD-87-CAC is a precision strip chart recorder for measuring and recording AC current. A clamp-on current probe is supplied and connects with two banana jacks on the side of the recorder case.

Specifications (RD-87-CAC)

AC Current Accuracy: ±5%
Probe Range: 0 to 300 Amps AC
Probe Dimensions: 158 x 73 mm (6.26 x 2.87")
Probe Opening: 28 mm (1.12")

Chart Ranges

0 to 50 A
0 to 100 A
0 to 250 A
0 to 300 A



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
RD-87-J	\$399	J-Type thermocouple recorder
RD-87-TEMP	399	Temperature recorder
RD-87-TRH	439	Temperature/humidity recorder
RD-87-VAC	399	AC voltage recorder
RD-87-CAC	439	AC current recorder
RD-87-MA	399	4 to 20 mA and DC voltage recorder

Comes complete with 1-pen per channel, 1 roll metric paper, 1 roll standard paper, 120 Vac power adapter, and complete operator's manual. **RD-87-J** includes a 6 foot beaded thermocouple wire. **RD-87-TEMP** includes 4 inch probe with 15 feet cable. **RD-87-TRH** includes a temperature/humidity probe with coiled cable. **RD-87-VAC** includes 2 sensor wires with banana plug and alligator clip. **RD-87-CAC** includes a clamp on current probe.

To order unit for 220 Vac, add suffix "-220V" to model number. No additional charge.

Ordering Example: RD-87-J, thermocouple recorder, JHSS-18U-RSC-12, handle probe, RD-87-RP-A, replacement paper, CT87-PEN-BLACK, replacement pen, \$399 + 41 + 20 + 8.50 = \$468.50. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$99), \$399 + 99 = \$498.

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners

Accessories

Model No.	Price	Description
RD-87-RP-A	\$20.00	Replacement paper, American scale, package of 4
RD-87-RP-M	20.00	Replacement paper, metric scale, package of 4
CT87-PEN-BLACK	8.50	Replacement black pen
CTH89-PEN-BLUE	8.50	Replacement blue pen (for RD-87-TRH)
CTH89-PEN-RED	8.50	Replacement red pen (for RD-87-TRH)
JHSS-18U-RSC-12	41.00	Handle probe, J type with retractable cable and SMP connector
MN1500	1.75	Batteries, alkaline 1.5 V "AA", 2/pack
OP-SET1/2	35.00	Reference Handbook: Temperature Measurement in Engineering Vol 1 & 2

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters