

# SANITARY THERMISTOR ASSEMBLIES

## Heavy-Duty with Protection Head




THS-H-NB9W Series

All Models



- ✓ Heavy-Duty Probe Design With Stepped Probe Stem for Additional Strength
- ✓ 1½" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting Standard
- ✓ White Polypropylene Head with Screw Cap Standard
- ✓ 316L SS Wetted Surfaces with 32 µin or Better Finish
- ✓ 10k Thermistor Element (44006) Standard
- ✓ -80 to 150°C (-112 to 302°F) Temperature Range

**For Use in CIP and Sanitary Processes**



THS-10K-H-0300-D1-NB9W, \$125, shown smaller than actual size.

### Options

- ✓ Fitting Styles
- ✓ Protection Heads
- ✓ Probe Lengths
- ✓ Thermistor Elements

The OMEGA® THS-H-NB9W Series thermistor probe assemblies are available in standard lengths from 3 to 6", with standard 10 kΩ (44006) thermistor element. These heavy-duty probes have a 3/8" diameter, which steps down to a 3/16" dia at the probe tip, for fast response and additional strength. Standard features include a 1½" 16 AMP Tri-Grip™ fitting, type NB9W white polypropylene protection head with screw cap. Please consult sales for available options, including element types and curves, probe lengths, protection heads and sanitary fitting styles.

### Element Options

Sensor Code	Resistance @ 25°C	Element Series
2K	2252 Ω	44004
3K	3000 Ω	44005
5K	5000 Ω	44007
30K	30,000 Ω	44008

For other thermistor elements, change the model number from "10K" to the desired sensor code as shown in the table above, no additional cost.

**MOST POPULAR MODEL HIGHLIGHTED!**

To Order (Specify Model Number)						
Model Number	Resistance at 25°C	Element Series	Interchangeability (0 to 70°C)	Sheath Dia.	Probe Length	
THS-10K-H-0300-D1-NB9W	10,000 Ω	44006	±0.2°C	¼"	3"	
THS-10K-H-0400-D1-NB9W	10,000 Ω	44006	±0.2°C	¼"	4"	
THS-10K-H-0500-D1-NB9W	10,000 Ω	44006	±0.2°C	¼"	5"	
THS-10K-H-0600-D1-NB9W	10,000 Ω	44006	±0.2°C	¼"	6"	


For lengths longer than 6", change "0600" in model number to the required length (eg, 12" = 1200, 9¼" = 0925)

To order with NB16W white polypropylene flip-top head, change model number suffix from "-NB9W" to "-NB16W"

To order with NB15 large 316 SS head, change model number suffix from "-NB9W" to "-NB15"

To order with NB13 medium size 316 SS head, change model number suffix from "-NB9W" to "-NB13"

**Ordering Example:** THS-10K-H-0400-D1-NB9W, 10,000 Ω thermistor sensor, 1½" 16 A Tri-Grip™ fitting, 4" length, heavy duty probe, NB9W white polypropylene screw cap protection head.



# SANITARY THERMISTOR ASSEMBLIES

## Standard Duty with Protection Head



THS-S-NB9W Series



**For Use in  
CIP and Sanitary  
Processes**


- ✓ Standard Duty 1/4" Probe Diameter
- ✓ 1 1/2" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting Standard
- ✓ White Polypropylene Head with Screw Cap Standard
- ✓ 316L SS Wetted Surfaces with 32 µin or Better Finish
- ✓ 10k Thermistor Element (44006) Standard
- ✓ -80 to 150°C (-112 to 302°F) Temperature Range

### Options

- ✓ Fitting Styles
- ✓ Protection Heads
- ✓ Probe Lengths
- ✓ Thermistor Elements

The OMEGA® THS-S-NB9W Series thermistor probe assemblies are available in standard lengths from 3 to 6", with standard 10 kΩ (44006) thermistor element. Standard features include a 1 1/2" 16 AMP Tri-Grip™ fitting, type NB9W white polypropylene protection head with screw cap. Please consult sales for available options, including element types and curves, probe lengths, protection heads and sanitary fitting styles.

**32 µin  
Polished  
Finish**



THS-10K-S-0300-D1-NB9W, \$95, shown smaller than actual size.

### Element Options

Sensor Code	Resistance @ 25°C	Element Series
2K	2252 Ω	44004
3K	3000 Ω	44005
5K	5000 Ω	44007
30K	30,000 Ω	44008

For other thermistor elements, change the model number from "10K" to the desired sensor code as shown in the table above, no additional cost.

**MOST POPULAR MODEL HIGHLIGHTED!**

To Order (Specify Model Number)						
Model Number	Price	Resistance at 25°C	Element Series	Interchangeability (0 to 70°C)	Sheath Dia.	Probe Length
THS-10K-S-0300-D1-NB9W		10,000 Ω	44006	±0.2°C	1/4"	3"
THS-10K-S-0400-D1-NB9W		10,000 Ω	44006	±0.2°C	1/4"	4"
THS-10K-S-0500-D1-NB9W		10,000 Ω	44006	±0.2°C	1/4"	5"
THS-10K-S-0600-D1-NB9W		10,000 Ω	44006	±0.2°C	1/4"	6"

For lengths longer than 6", change "0600" in model number to the required length (eg, 12" = 1200, 9 1/4" = 0925)

W white polypropylene flip-top head, change model number suffix from "-NB9W" to "-NB16W" and add \$7 to price.

To order with NB15 large 316 SS head, change model number suffix from "-NB9W" to "-NB15"

To order with NB13 medium size 316 SS head, change model number suffix from "-NB9W" to "-NB13"

**Ordering Example:** THS-10K-S-0400-D1-NB9W, 10,000 Ω thermistor sensor, 1 1/2" 16 A Tri-Grip™ fitting, 4" length, standard duty probe, NB9W white polypropylene screw cap protection head,

S-X



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters