

Mix and Match Series Digital Stem Thermometers

Deluxe Digital Pocket Thermometer

Model HH65

\$20



- ✓ Data Hold
- ✓ F°/C° Switch
- ✓ ON/OFF Switch
- ✓ Auto Power OFF: 10 min

- ✓ 63.5 mm (2.5") x 3.2 mm (1/8" Dia.) Probe
- ✓ -40 to 150°C (-40 to 300°F)
- ✓ 15 sec Response Time
- ✓ Pocket Clip
- ✓ Protective Cover
- ✓ Drop Resistant
- ✓ Water Resistant
- ✓ ±2% Accuracy
- ✓ 1° Resolution



Case Included

Digital Min/Max Thermometer


Model TPD40

\$21



- ✓ °F/°C Switch
- ✓ ON/OFF Switch
- ✓ Clear Button
- ✓ Plastic Sheath
- ✓ Pocket Clip
- ✓ -26 to 200°C (-14 to 392°F)
- ✓ 127 mm (5") Stainless Steel Probe
- ✓ Accuracy: ±1°C (1.8°F) from -10 to 82°C (14 to 180°F)

Specifications	TPD41
Measurement Range	-50 to 150°C (-58 to 302°F)
Accuracy	±1°C between -20 and 120°C, otherwise, ±2°C; ±2°F between -4 and 248°F, otherwise, ±4°F
Probe Size	03.5 x 125 mm (5/16 x 5")
Sampling Time	1 Second or 10 Seconds Selectable
Unit Weight	20 g (with Probe Cover) (0.7 oz)
Unit Size	03.5 x 11 mm (5/16 x 7/16")
Display Resolution	0.1° between -19.9 to 199.9°, otherwise, 1°
Display Digit Size	7 H x 3 mm W (5/16 x 3/16")
Battery	1.5 V x 1 pc, Model MN-TPD
Ambient Temperature	-10 to 50°C (14 to 122°F)



Battery: 15 V x 1 pc LR-43
Dimensions: 165 L x 13 W x 13 mm H (6 1/2 x 1/2 x 1/2")

Protective Case Included

Cheaper by the Dozen
Purchase Any Combination of 12 Units and Save 20%

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Easy To Read 51 mm (2") Dia. Thermometer

Model TPD42
\$35

Shown close to actual size

Specifications	TPD42
Measurement Range	-50 to 150°C (-58 to 302°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C/±2°F from -4 to 248°F, otherwise, ±4°F
Probe Size	03.5 x 125 mm (5/16 x 5")
Sampling Time	1 Second
Unit Weight	20 g (with Probe Cover) (0.7 oz)
Unit Size	03.5 x 11 mm (5/16 x 7/16")
Display Resolution	0.1° from -19.9 to 199.9° otherwise, 1°
Display Digit Size	7 H x 3 mm W (5/16 x 3/16")
Automatic Power Off	After 10 minutes
Battery	1.5 V x 1 pc, Model MN-TPD
Ambient Temperature	-10 to 50°C (14 to 122°F)
Button Functions	1) ON/OFF and Hold with °C 2) ON/OFF and Hold with °F 3) ON/OFF and °C/°F



Case Included

Pocket Thermometer



Model TPD41

\$18

Case Included



- ✓ Low Cost
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover

Applications: Air Conditioning, Food Processing, Heating and Ventilating, Agriculture, Automobile, Brewing, Photography, Food Storage, Refrigeration, Pharmaceutical and Laboratory uses.

Mix and Match Series Digital Stem Thermometers



Model TPD34/35
\$18/22

**Cheaper
by the Dozen**
 Purchase Any
 Combination
 of 12 Units and
 Save 20%

- ✓ On/Off Switch
- ✓ Data Hold Function
- ✓ °C or °F Switchable
- ✓ Automatic Power Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover



Case Included

Model TPD32/33
\$21/23



- ✓ On/Off Switch
- ✓ Data Hold Function
- ✓ °C or °F Switchable
- ✓ Automatic Power Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover

**ALL MODELS
AVAILABLE
FOR FAST
DELIVERY!**


Case Included



Specifications	TPD32	TPD33
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4°F to -58 and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	03.5 x 125 mm (5/8 x 5")	03.5 x 200 mm (5/8 x 8")
Sampling Time	1 Second	0.5 Second
Unit Weight	23 g (with Probe Cover) (0.7 oz)	28 g (with Probe Cover) (0.9 oz)
Unit Size	5 x 58 mm (5/8 x 2 1/8")	
Display Resolution	0.1° from -19.9 to 199.9°; otherwise, 1°	
Display Digit Size	6 H x 3 mm W (5/8 x 3/16")	
Auto Power Off	After 10 minutes	
Battery	1.5 V x 1pc, Model PH-BATT-3	
Ambient Temp.	-10 to 50°C (14 to 122°F)	
Button Functions	ON/OFF and °C/°F	

Specifications	TPD34	TPD35
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4 to -58°F and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	03.5 x 125 mm (5/8 x 5")	03.5 x 200 mm (5/8 x 8")
Sampling Time	1 Second	0.5 Second
Unit Weight	21 g (with Probe Cover) (0.7 oz)	26 g (with Probe Cover) (0.9 oz)
Unit Size	03.5 x 11 mm (5/8 x 7/16")	
Display Resolution	0.1° from -19.9 to 199.9°; otherwise, 1°	
Display Digit Size	7 H x 3 mm W (5/8 x 3/16")	
Auto Power Off	After 10 minutes	
Battery	1.5 V x 1pc, Model No. MN-TPD	
Ambient Temp.	-10 to 50°C (14 to 122°F)	
Button Functions	ON/OFF and °C/°F	

Case Included



- ✓ On/Off Switch
- ✓ Data Hold Function
- ✓ °C or °F Switchable
- ✓ Automatic Power Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover

Model TPD38/39
\$23/24



Specifications	TPD38	TPD39
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4°F to -58 and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	3.5 x 200 mm (5/8 x 8")	3.5 x 200 mm (5/8 x 8")
Sampling Time	1 Second	0.5 Second
Unit Weight	23 g (with Probe Cover) (0.8 oz)	28 g (with Probe Cover) (0.99 oz)
Unit Size	0.20 x 72 mm	
Display Resolution	0.1° from -19.9 to 199.9°; otherwise, 1°	
Display Digit Size	6 H x 3 mm W (5/8 x 3/16")	
Auto Power Off	After 10 minutes	
Battery	1.5 V x 1pc, Model PH-BATT-3	
Ambient Temp.	-10 to 50°C/14 to 122°F	
Button Functions	ON/OFF and °C/°F	


Model TPD36/37
\$17/21



- Temperature Tester
- ✓ On/Off Switch
 - ✓ Data Hold Function
 - ✓ °C or °F Switchable
 - ✓ Automatic Power Off
 - ✓ Stainless Steel Probe
 - ✓ Protective Probe Cover

Specifications	TPD36	TPD37
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4°F to -58 and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	03.5 x 125 mm (5/8 x 5")	03.5 x 200 mm (5/8 x 8")
Sampling Time	1 Second	0.5 Second
Unit Weight	21 g (with Probe Cover) (0.7 oz)	26 g (with Probe Cover) (0.9 oz)
Unit Size	36 L x 17 H x 33 mm D (1 1/2 x 1 1/8 x 1 1/8")	
Display Resolution	0.1° from -19.9 to 199.9°; otherwise, 1°	
Display Digit Size	7 H x 3 mm W (5/8 x 3/16")	
Auto Power Off	After 10 minutes	
Battery	1.5 V x 1pc, Model No. PH-BATT-3	
Ambient Temp.	-10 to 50°C/14 to 122°F	
Button Functions	ON/OFF and °C/°F	

Case Included



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters