# Strain, Process & MONOGRAM'S ERIES Temperature Meters with Optional Relays and Analog Output

\$245
Basic Unit



## **Inputs**

✓ Thermocouple

✓ RTD

Process (dc Voltage and Current)

Strain Gage

**Options** 

Relay Output with Adjustable Deadband

Isolated or Non-Isolated Analog Output

✓ Totally Programmable Color Display

Low Voltage Power Options

### **Panel Meters/Controllers**

OMEGA® DP25B Series feature the biggest, brightest display of any ½ DIN panel meter. The user can select the display color: **RED**, **AMBER**, or **GREEN**.

The unparalleled accuracy of the OMEGA® DP25B signal conditioner is available in an economical series of panel meters/controllers. The OMEGA® DP25B series of meter/controllers feature a four-digit 9-segment display plus optional dual 5 amp SPDT relays (Single Pole Double Throw; Form C) and a choice of isolated or non-isolated analog output. The scalable 0 to 10 Vdc, 0 to 20 mA, or 4 to 20 mA analog output can be used for retransmission of the display value or as a proportional control output, as required. The microprocessor-based DP25B series includes instruments for process (dc voltage and current) strain gage, thermocouple, and RTD.

### **Common Specifications**

**Display:** 4-digit, 9-segment, 21 mm (0.83") Red, Amber or Green LED (programmable) **Analog-to-Digital Technique:** Dual slope

Internal Resolution: 15-bit

Polarity: Automatic Read Rate: 3/sec

Step Response: 2 seconds

Relay Outputs (optional): 2 Form C (SPDT) relays, rated 5 Amp 250 Vac; programmable for active high/low alarms with latching/non-latching relays.

Analog output (optional): 0 to 10 V, 4 to 20 mA or 0 to 20 mA; can be assigned to a display range (scalable) or proportional control output with setpoint

#1 when used as a control output

**Power:** 115 Vac or 230 Vac ±10%, 10 to 32 Vdc, 26 to 56 Vdc; 8 Watts max (DP25B-TC or -RTD), 11 Watts max (DP25B-E or -S); 240 V RMS

overvoltage protection



### Thermocouple and RTD Models

The DP25B Series for thermocouple and RTD inputs is a versatile panel meter and limit alarm in one easily programmable instrument. The DP25B-TC is selectable for J, K, T, or J DIN thermocouples. The DP25B-RTD accepts 100  $\Omega$  PT (0.00385 curve) RTD's.

Covered by U.S and

International patents and pending applications

### **DP25B-TC (Thermocouple)**

Input Type	Range		Accuracy
J	-210 to 760°C	-346 to 1400°F	
K	-270 to 1372°C	-454 to 2500°F	0.5°C (0.9°F)
T	-210 to 400°C	-346 to 752°F	0.5 0 (0.9 F)
J DIN	-200 to 900°C	-328 to 1652°F	

**Isolation:** Dielectric strength to 2500 V transient per 3 mm spacing based on EN 61010 for 260 Vrms or DC.

NMR: 60 dB CMR: 120 dB

Operating Temperature: 0 to 50°C (32 to 122°F) Storage Temperature: -40 to 85°C (-40 to 185°F)

Relative Humidity: 90% @ 40°C (104°F)

(non-condensing)

Dimensions: 48 H x 96 W x 152 mm D

(1.89 x 3.78 x 6.0")

Panel Cutout: 45 x 92 mm (1.772 x 3.622")

**Weight:** 36 g (1.27 lb)

Thermocouple Meter Specifications

**Input:** Thermocouples types, J, K, T, and J DIN **Relay Hysteresis:** Programmable from 0 to 9999 **Accuracy:** ±0.50°C (0.9°F) after 30 min. warm-up

Temperature Coefficient: ±50 PPM/°C

Input Resistance: 100 M $\Omega$ 



#### DP25B-TC: Programmed for Green Display

### Process and Strain Models

The DP25B-E process and strain meters accept a wide range of dc voltage and current inputs to cover any typical process application. They feature easy front panel scaling to virtually any engineering units, selectable excitation of four voltages to work with most transducers and transmitters, front panel and remote tare function for weighing applications, and a hardware lockout to prevent unauthorized changes in set-up.

### DP25B-RTD (RTD)

Input Type		Range	Accuracy	
	RTD, 100 Ω Pt,	-200 to 850°C	0.5°C	
	2, 3, 4-wire	(-328 to 1562°F)	(0.9°F)	

# RTD Temperature Meter/Controller Specifications

**Input:** RTD 100  $\Omega$  Pt (0.00385 curves)

2-, 3- and 4-wire selectable

Accuracy: ±0.50°C (0.9°F) after 30 min. warm-up

Temperature Coefficient: ±50 PPM/°C

Input Resistance: 100 M $\Omega$ 

# DP25B-E (Process) / DP25B-S (Strain)

Input Type	Range	Accuracy
mV, V, mA	0-100 mV, ±50 mV, 0-10 V ±5 V, 0-20 mA, 4-20 mA	0.02% Rdg

# Process & Strain Meters / Controllers Specifications

Input Ranges: 0 to 100 mV, ±50 mV, 0 to 10 V, ±5 V,

0 to 20 mA, 4 to 20 mA

Protection: 240 V rms max for voltage input ranges;

200 mA for current ranges

**Input Impedance:** 100 M $\Omega$  for 100 mV or  $\pm$ 50 mV range; 1 M $\Omega$  for 10 V or  $\pm$ 5 V range;

5  $\Omega$  for 20 mA current input

Analog-to-Digital Technique: Dual slope

Internal Resolution: 15-bit

Polarity: Automatic

Max Error Strain/Process: ±0.03% rdg

Span Tempco: ±50 ppm/°C

Warmup to Rated Accuracy: 30 min

Excitation Voltage: 24 V @ 25 mA or 12 V @ 50 mA;

10 V @ 120 mA or 5 V @ 60 mA




# **Select Your Color!**

Program to display in RED, AMBER, or GREEN.

# **Totally Programmable Color Displays**

The OMEGA® DP25B Series meters and controllers have totally programmable color displays. The display can be programmed for RED, AMBER, or GREEN.





### **CUSTOM CONFIGURATIONS**

Custom firmware and hardware available in quantity



Custom color bezels and enclosures are available for Original Equipment Manufacturers.

Enhance the appearance of your equipment design with custom colors.

Consult the OMEGA® OEM GROUP










The following LVD (Low Voltage Directive/Safety) requirements have been met to comply with EN 61010-1, 1993 (Electrical equipment for measurement, control and laboratory use)

1. Pollution Degree 2 2. Installation Category II 3. Double Insulation DP25/DP26/PHCN-37/ORCN-37/OPCN-37 complies with the following EMC Immunity Standards as tested per EN 50082-2, 1995 (Industrial environment)

· ·	, ,	•
Phenomena	Test Specification	Basic Standard
Electrostatic Discharge	+/- 4 kV contact discharge +/- 8 kV air discharge	IEC 1000-4-2 Perf. Criteria B
Radio Frequency electromagnetic field	27 - 1000 MHz 10 V/m 80% AM (1 KHz)	IEC 1000-4-3 Perf. Criteria A
Fast Transients	+/- 2 kV (ac mains) +/- 1 kV (dc, signal I/O) 5/50 ns Tr/Th, 5 KHz repit. Freq.	IEC 1000-4-4 Perf. Criteria B
Radio Frequency conducted	0.15 - 80 MHz 10 V/m 80% AM (1 KHz)	IEC 1000-4-6 Perf. Criteria A
Surges	+/- 2 kV line to earth +/- 1 kV line to line 1.2/50 (8/20) _s Tr/Th	IEC 1000-4-5 Perf. Criteria B
Voltage Dips	30% reduction 10 ms 60% reduction 100 ms	IEC 1000-4-11 Perf. Criteria B
Voltage Interruption	>95% reduction 5000 ms Perf. Criteria C	IEC 1000-4-11

DP25/DP26/PHCN-37/ORCN-37/OPCN-37 comply with the following EMC Emission Standards as tested per EN 50081-1, 1997 (Residential, Commercial and Light Industrial)

Phenomena	Frequency Range	Limits	Basic Standard
Radiated Emission	30 - 230 MHz 230 - 1000 MHz	30 dB_V/m at 10 m 37 dB_V/m at 10 m quasi peak	CISPR 22 Class B
Conducted Emission	0.15-0.5 MHz 0.5-5 MHz 5-30 MHz	66-56 dB_V q.peak 56 dB_V quasi peak 60 db_V quasi peak	CISPR 22 Class B



To Order (Specify Model No.)		
<b>Basic Model</b>	<b>Description</b> Price	
DP25B-TC	Thermocouple \$245	
DP25B-RTD	RTD	245
DP25B-E	Process (dc voltage and current)	245
DP25B-S	Strain input	245

### **Power Options\***

Order Suffix	Add'l Price	Power
-230	N/C	230 Vac
-DC10/32	\$95	10 to 32 Vdc
-DC26/56	120	26 to 56 Vdc

### **Output Options\***

Order Suffix	Add'l Price	Power
-A	\$80	Analog output
-AI	90	Isolated analog output
-R	70	Dual 5 A relays

\*Not field installable. For -AI option, the -R option is required. All units come complete with a operator's manual. **Ordering Example: DP25B-TC-DC10/32-AR**, thermocouple indicator for J, K, T or J DIN input, low voltage power, analog output and dual 5 A relays, \$245 + 95 + 80 + 70 = **\$490** 

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

# www.omega.co.uk



# UNITED STATES

www.omega.com 1-800-TC-OMEGA Stamford, CT.

#### **CANADA**

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

#### **GERMANY**

www.omega.de Deckenpfronn, Germany 0800-8266342

### **UNITED KINGDOM**

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622

www. omega.co.uk Manchester, England 0800-488-488 +44-(0)161-777-6611

#### **FRANCE**

www.omega.fr 0800-466-342

#### **BENELUX**

www.omega.nl 0800-099-33-44



Sales@omega.co.uk

# More than 100,000 Products Available!

### Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

# pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

## Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ehernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters