# **Handheld Relative Humidity Meters**

RH-202 Series Starts at



## Common Features

- Magnified Display
- Separate Battery Compartment
- ✓ RH Accuracy±2%
- -10 to 100°C (14 to 212°F)

## RH-202 Features

- ✓ Waterproof to IP65 (With Plug Connected)
- Backlight
- Auto Switch-Off
- °C/°F/RH Selection Button

## **RH-202L Features**

- Connector for Type K Thermocouple
- Max/Min Averaging
- Display Hold
- ✓ Logging (250 Readings) on Demand or Preset Interval)
- ✓ Data Store with 4-Digit **Data Code Input**
- Dewpoint Measurement
- Auto Range/Range Lock

## A New Range of Handheld Relative **Humidity Instruments**

The range has been specifically designed in response to demand for the effective and reliable measurement of controlled environments. Featuring 2 models, RH-202 and RH-202L with the latter including functions: dewpoint, calculation, separate thermocouple input and logging.

### **Performance**

The RH202 meters from OMEGA® offer the user the highest accuracies for a budget price.

The ergonomic case design with advanced technology sensors combine to give an instrument with excellent performance and long life.

The RH-202L features an external temperature probe option for pinpoint temperature measurement. 250 readings can be logged, replayed on the screen and output to a printer or PC using the HHP-2000-DL. Each reading is user coded and time and date stamped.

## **Dewpoint**

The dewpoint is defined as the lower temperature to which air must be cooled in order for condensation (saturation) to occur. The dew point is dependent on the concentration of water vapor present, and, therefore, the relative humidity.

## **Simple Data Collection** and Analysis

The RH-202L features special logging functions that enable readings to be taken, stored, retrieved and downloaded in the shortest possible time. This reduces the risk of clerical errors and saves writing and keying-in time when analysis is needed.

## Logging on Demand

Logging on Demand allows readings to be stored when required, with the ability to add a 4-digit reference number (including decimal point) to each reading and record the date and time each reading is taken. This function is excellent for helping you cut down on paperwork and clerical errors. It is ideally suited to tasks where you wish to maintain a record of the time and date when a temperature was taken.

## **Preset Interval Logging**

Preset interval logging lets you determine the frequency at which readings are taken. Once the instrument has been set, readings



RH-202L, \$575, shown actual size.



Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy. Order a Spare! Model No. SC-GG-KI-30-1M, £10.

Specifications	RH-202	RH-202L	
Sensor(s)	Pt100 + capacitive RH sensor	Pt100 + capacitive RH sensor input for Type K thermocouple (SMP type)	
Range	0 to 100% RH, -10 to 100°C (+14 to 212°F)	0 to 100% RH, -10 to 100°C (+14 to 212°F)	
Resolution	0.1% RH, 0.1°	RH 0.1%, Temperature 0.1° from -199.9 to +199.9°, 1° elsewhere	
Accuracy	±2% RH, 0 to 80% RH ±3% RH, 80 to 100% RH ±0.5°C/1°F 0 to ±80°C/±32 to 176°F ±1°C, 2°F elsewhere	±2% RH, 0 to 80% RH ±3% RH, 80 to 100% RH ±0.5°C/1°F 0 to +80°C/+32° to 176°F ±1°C, 2°F elsewhere ±0.2% reading ±2 digits for K thermocouple input	
Operating Temperature	0 to 50°C	0 to 50°C	
Operating Humidity	0 to 100% RH(non-condensing)	0 to 100% RH(non-condensing)	
Battery Type	2 (AA) or equivalent cells	2 (AA) or equivalent cells	
Battery Life	Typically 150 Hours	Typically 150 Hours	
Low Battery Check	symbol appears on display	symbol appears on display	
Display	12.7 mm (0.5") custom LCD	12.7mm (0.5") custom LCD	
Back Light	Yes	Yes	
Environmental Specifications	IP65 with plug connected		
Dimensions	155 x 67 x 40 mm (6.1 x 2.6 x 1.6")	155 x 67 x40 mm (6.1 x 2.6 x 1.6")	
Weight	180 g (6.4 oz)	180 g (6.4 oz)	

are taken automatically at the interval you decide (from once every minute to once every 24 hours), providing an excellent means of troubleshooting and examining trends over a given period of time. With preset interval logging, you really can "set it, forget it" as the instrument will continue logging until a maximum of 250 readings are taken or your data is downloaded.

## **Data Analysis**

Data can be viewed and analyzed direct from the magnified display. By simply pressing a few keys you can scroll through your readings with ease. You may then download the data to a PC or Epson compatible printer via OMEGA's HHP-2000-DL. Data can then be analyzed using our OM-MLWIN.

## Data Download with the HHP-2000-DL

Access to stored information is gained via OMEGA's infrared HHP-2000-DL, which is designed to give users a quick and simple means of retrieving and downloading data. Information can be output direct to either an Epson compatible printer for immediate study or downloaded to a PC for more detailed analysis.

## Data Analysis with OM-MLWIN for Windows

OMEGA® has created a Windows software package enabling information to be put into

spreadsheets and charts for incorporating into reports and other documents. Even separate reports from different units can be merged to produce one report.

PC analysis really couldn't be any simpler. By following the software's simple menu instructions, you will find it easy to view and manipulate information to your individual requirements. For example, once a logging session is complete, all you need to do in order to gain access to information stored within the instrument is position the PC's cursor over the "Retrieve Data" menu icon, click once and press a button on the instrument. Information is then automatically

transferred, via the infrared link and stored within the computer.

You may display the retrieved information in graph format by positioning the cursor over the "Display As Graphical Data" menu icon and click again. You can access the graph produced to highlight certain areas or key data points, prior to printing or exporting the graph into other software packages.

Furthermore, all graphs show the identification number of the instrument used, enabling data to be cross-checked against calibration records helping to ensure full traceability.

## ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)			
Model No.	Price	Description	
RH-202	£345	Handheld thermohygrometer	
RH-202L	385	Handheld thermohygrometer with datalogging	

Comes with RH/Temp probe, rubber boot, 2 "AA" batteries and complete operator's manual. **Ordering Examples:** RH-202, handheld thermohygrometer, £345.

**RH-202L**, handheld thermohygrometer with datalogging, plus **CAL-3-HU**, Traceable calibration, and **OM-MLWIN**, Windows software, £385 + 84 + 10 = £479.

#### **Accessories**

Model No.	Price	Description
CAL-3-HU	£90	Traceable calibration
HHP-2000-DL	80	Infrared download box and data link
OM-MLWIN	10	Windows software (requires 4MB RAM and Windows 3.1x or 95)
HHP-2000-RB	20	Spare rubber boot

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622

Fax +44(0) 161 777 6622

Sales@omega.co.uk

## www.omega.co.uk



## **UNITED STATES**

www.omega.com 1-800-TC-OMEGA Stamford, CT.

### **CANADA**

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

#### **GERMANY**

www.omega.de Deckenpfronn, Germany 0800-8266342

#### UNITED KINGDOM

www. omega.co.uk Manchester, England 0800-488-488

## **FRANCE**

www.omega.fr 088-466-342

#### **CZECH REPUBLIC**

www.omegaeng.cz Karviná, Czech Republic 596-311-899

#### **BENELUX**

www.omega.nl 0800-099-33-44



## More than 100,000 Products Available!

## Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

## Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

## pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

## Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

## Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters